

malcom

SOLDER PASTE SOFTENER

SPS SERIES


Can mix and soften the solder paste easily



SPS-1, SPS-2

SPECIAL FEATURES

- Employs a Pseudo-Planetary Motion combined the revolution and the rotation.
- The centrifugal force causes the solder paste repeatedly fold over itself thereby mixing and softening the paste.
- Can select single or dual jar.




ITEM	SPECIFICATION
Mixing Method	Pseudo-Planetary Motion
Centrifugal Force	Under 50kPa (0.5kgf/cm ²)
Built - in Timer	Setting from 1 to 99 minutes
Paste Container Sizes	Solder Paste 500g : Container Size 100cc 1kg : Container Size 300cc
Rotation Balance (SPS-1 only)	Auto Balancing
Safety Interlocks	Door switch and lock/ Unbalanced motion detector
Power Supply	100VAC, 110VAC, 220VAC and 240VAC 30W 50/60 Hz
Substantial Power Supply (SPS-1 only)	Alkaline Battery : Size AA Battery×4 for Auto Balancer
Weight	Approx. 20 kg

SPS-5

SPECIAL FEATURES

- Designed especially for the non-intrusive mixing of solder paste in cartridges.
- Automated operation provides an even consistency of solder paste for viscosity and temperature.
- Cartridge can be taken from the refrigerator to screen printer in about 10 minutes.



ITEM	SPECIFICATION
Mixing Method	Pseudo-Planetary Motion
Centrifugal Force	Under 50kPa (0.5kgf/cm ²)
Built-In Timer	Setting from 1 to 99 minutes
Paste Container Sizes	Up to 2 kg Cartridge
Balance	Dual Cartridges
Safety Interlocks	Door switch and lock/ Unbalanced motion detector
Power Supply	100VAC, 110VAC, 220VAC and 240VAC 30W 50/60 Hz
Weight	Approx. 40 kg

※ The above specifications are subject to change without notice.

Representative

MALCOMTECH INTERNATIONAL
26200 INDUSTRIAL BLVD.
HAYWARD, CA 94545
(510) 293-0580 • FAX (510) 293-0940